

**BPI Lens Dryer™
& Production
Lens Dryer™**

**For use only by qualified
personnel in a
laboratory environment.**

**Due to high operating
temperature, access
should be restricted.**

Specifications

The BPI Lens Dryer is a system which filters warm air to dry lenses in seconds. Optional on/off foot pedal, 115 v. or 220v. model

The BPI Production Lens Dryer is a high volume lens dryer with built in timer available in 115 or 220 volt model. Front switch allows for continuous drying.

For use only by qualified personnel in a laboratory environment.

Unpacking

When unpacking your system, please check to ensure that no concealed damage occurred in transit. If such is noted, save the shipping carton and immediately notify the shipping company's damage control inspector in your area so a claim may be processed. Failure to do this may void any future claim and replacement. Also, call BPI Customer Service so arrangements for a replacement may be made.

BPI Lens Dryer™

HEIGHT	WIDTH	LENGTH	VOLTAGE	WEIGHT	FUSE	AMPERAGE
8.75 in.	7 in.	7.5 in.	110v or 220v.	8 lbs.	10 amps	2 amps
22.22 cm	17.78 cm	19.05 cm		3.62 kg		

BPI Production Lens Dryer™

HEIGHT	WIDTH	LENGTH	VOLTAGE	WEIGHT	FUSE	AMPERAGE
11.5 in.	18 in.	26 in.	110v or 220v.	30 lbs.	20 amps	4 amps
29.21 cm	45.72 cm	66.04 cm		13.6 kg		



**BPI Lens Dryer™
& Production
Lens Dryer™**

Setting Up

Connect unit to a convenient outlet. If unit came with optional foot pedal, connect the power supply of the unit to the foot pedal and the foot pedal to a convenient outlet.

Questions? Ordering...

For information about any BPI product and to order supplies, please give us a toll-free call at the number shown for your area.